



CERTIFICATE OF ANALYSIS

ERM®-FA006

POLYMETHYLMETHACRYLATE			
	Weight averaged molar mass M _w		
Molar mass M _w ¹⁾	Certified value 3) [g/mol]	Uncertainty ⁴⁾ [g/mol]	
	365500	10800	
Viscosity ²⁾	Intrinsic viscosity [η]		
	Certified value 3) [mL/g]	Uncertainty ⁴⁾ [mL/g]	
	90.63	1.05	

¹⁾ obtained by laser light scattering

This certificate is valid for five years after purchase. This validity may be extended as further evidence of stability becomes available.

Sales date:

The minimum amount of sample to be used is 10 mg.

Accepted as an ERM®, Berlin,

Latest revision Berlin, 2018-01-18

BAM Berlin Department I Analytical Chemistry; Reference Materials 12200 Berlin, Germany BAM Berlin Division I.3 Structural Analysis 12200 Berlin, Germany

Dr. Franziska Emmerling (Head of Department)

Dr. Steffen Weidner (Study Director)

²⁾ obtained by viscometry using an UBBELOHDE viscometer according to DIN 51562 - 1

³⁾ Unweighted mean value of the means of accepted sets of data, each set being obtained in a different laboratory. The certified value is traceable to the International System of units (SI).

⁴⁾ The certified uncertainty is the expanded uncertainty estimated in accordance with the Guide to the Expression of Uncertainty in Measurement (GUM) with a coverage factor k = 2, corresponding to a level of confidence of about 95 %. The certified uncertainty value is traceable to the International System of units (SI).

Indicative Values		
	Weight-averaged molar mass M _w	
Molar masses ¹⁾	Indicative value ²⁾ [g/mol]	Uncertainty 3) [g/mol]
	365900	11800
	Number-averaged molar mass M _n	
	Indicative value ²⁾ [g/mol]	Uncertainty 3) [g/mol]
	294000	13500
	z-averaged molar mass M _z	
	Indicative value ²⁾ [g/mol]	Uncertainty 3) [g/mol]
	402300	13400
	Molar mass at peak maximum M _p	
	Indicative value ²⁾ [g/mol]	Uncertainty 3) [g/mol]
	402900	14700

¹⁾ obtained by Size Exclusion Chromatography (SEC) according to DIN 55672

³⁾ The certified uncertainty is the expanded uncertainty estimated in accordance with the Guide to the Expression of Uncertainty in Measurement (GUM) with a coverage factor k = 2, corresponding to a level of confidence of about 95 %

Additional Material Information		
Glass transition temperature T _g	123.7 °C ¹)	
Density	1.21 g/mL ²⁾	
Melt flow index	0.16 g / 10 min	

¹⁾ obtained by Differential Scanning Calorimetry (DSC)

Certificate ERM®-FA006 Page 2 of 4

²⁾ Unweighted mean value of the means of accepted sets of data, each set being obtained in a different laboratory.

²⁾ at 25°C according to DIN EN ISO 1183-1

^{3) 21.6} kg at 230°C according to DIN EN ISO 1133

NOTE

European Reference Material ERM®-FA006 was originally certified as BAM-P06. It was produced and certified under the responsibility of Bundesanstalt für Materialforschung und –prüfung (BAM) according to the principles laid down in the technical guidelines of the European Reference Materials® co-operation agreement between BAM-LGC-IRMM. Information on these guidelines is available on the Internet (http://www.erm-crm.org).

DESCRIPTION OF THE SAMPLE

The material was synthesised by different polymerization procedures, and purified by dissolution and precipitation. A detailed homogeneity study was performed. The material identity was confirmed by Proton Nuclear Magnetic Resonance (NMR) and Infrared (IR) Spectroscopy. The sample consists of a white, amorphous material. It was bottled in glass vials with a unit size from 1 to 10 g.

ANALYTICAL METHOD USED FOR CERTIFICATION

- Size Exclusion Chromatography according to DIN 55 672 1 (GPC using tetrahydrofurane as eluent)
- Laser Light Scattering
- Viscometry according to DIN 51 562 1 (Viscometry: Determination of kinematic viscosity using a Ubbelohde – Viscometer, Part1: Design and realisation of measurements

Details on the procedure for analysis can be found in the corresponding certification report.

PARTICIPANTS

Aventis, Frankfurt / M.

Bundesanstalt für Materialforschung und -prüfung, Berlin

Bayer AG, Uerdingen

Bayer AG, Leverkusen

Bundeskriminalamt, Wiesbaden

BMW, Dingolfing

Fraunhofer Institut für Angewandte Polymerforschung, Teltow

RWTH Aachen, Institut für Kunststoffverarbeitung

Institut für Lacke und Farben, Magdeburg

Institut für Polymerforschung, Dresden

Martin-Luther-Universität, Halle-Wittenberg

Max-Planck-Institut für Polymerforschung, Mainz

Polymer Standards Service GmbH, Mainz

Röhm GmbH, Darmstadt

RWTH Aachen, Institut für Textilchemie und Makromolekularen Chemie

Goldschmidt AG, Essen

Technische Universität Dresden

Universität Bayreuth

Universität Erlangen-Nürnberg

Universität Essen

Universität Freiburg

Universität Hamburg, Institut für Technische und Makromolekulare Chemie

Universität Leipzig

Johannes-Gutenberg-Universität Mainz, Institut für Makromolekulare Chemie

Johannes-Gutenberg-Universität Mainz, Institut für Physikalische Chemie

Universität Osnabrück

Universität Stuttgart, Institut für Technische Chemie

Universität Stuttgart, Institut für Textil- und Faserchemie

Universität Ulm

Universität - Gesamthochschule Siegen

Viscotek GmbH, Weingarten

Certificate ERM®-FA006 Page 3 of 4

SAFETY INFORMATION

Specific safety information are not known

INSTRUCTIONS FOR USE

Before withdrawing a sample the bottle has to reach room temperature. After use, the bottle has to be closed and stored at the recommended temperature.

STORAGE

Samples have to be stored at $5 \pm 2^{\circ}$ C.

However, BAM cannot be held responsible for changes that happen during storage of the material at the customer's premises, especially of opened samples.

LEGAL NOTICE

Neither BAM, its contractors nor any person acting on their behalf:

- (a) make any warranty or representation, express or implied, that the use of any information, material, apparatus, method or process disclosed in this document does not infringe any privately owned intellectual property rights; or
- (b) assume any liability with respect to, or for damages resulting from, the use of any information, material, apparatus, method or process disclosed in this document save for loss or damage arising solely and directly from the negligence of BAM.

NOTE

A detailed technical report describing the production, characterisation as well as the analytical procedures applied and the treatment of the analytical data used to certify ERM®- FA006 is available on request from BAM.

Supply of Reference Materials by Bundesanstalt für Materialforschung und -prüfung:

Richard-Willstätter-Straße 11, 12489 Berlin, Germany Phone: +49 30 8104 2061 – Fax: +49 30 8104 72061 e-mail: sales.crm@bam.de – internet: www.bam.de

Certificate ERM®-FA006 Page 4 of 4